


## Product data sheet

### Characteristics

# 33659

## MX shunt trip release, Compact NS 630b to Compact NS 3200, 24VDC to 30VDC, 24 VAC 50/60 Hz



### Main

Device short name	MX
Product or component type	Voltage release
Device application	Control
Range compatibility	MasterPact NT MasterPact NW ComPact NS630b...1600 ComPact NS1600b...3200
Voltage release type	Shunt trip release
[Uc] control circuit voltage	24 V AC 50 Hz 24...30 V DC

### Complementary

Threshold tripping voltage	0.7...1.1 x Un
Supply holding power	4.5 VA
Mounting mode	Fixed
Response time	50 ms (Compact NS630b...1600) 50 ms (Compact NS1600b...3200) 55 ms (MasterPact NT) 70 ms (MasterPact NW)
Accessory / separate part category	Spare parts for MasterPact NT Spare parts for MasterPact NW Spare parts for Compact NS1600b...3200 Spare parts for Compact NS630b...1600

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	150.0 g
Package 1 Height	3.3 cm
Package 1 width	6 cm
Package 1 Length	8.4 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	1.57 kg
Package 2 Height	9 cm
Package 2 width	18.5 cm
Package 2 Length	13.2 cm
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Weight	19.303 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------