

## Product data sheet

### Characteristics

# A9HKS532

## Acti 9 - PK P&S - single door - 32A - 5 pin



### Main

Range	Acti 9
Product name	PK P&S Units
Product or component type	Consumer unit
Device application	Power socket distribution
Colour	White (RAL 9003)

### Complementary

Product compatibility	PK panel-mounted straight socket
Enclosure mounting	Surface Flush
[In] rated current	32 A
Pin number	5
Total number of 18 mm modules	4
Enclosure/cubicle description	Single door enclosure
Enclosure material	Galvanized steel box Galvanized steel DIN rail Galvanized steel cable gland plate CRCA front plate
Height	305 mm external:
Width	138 mm external:
Depth	65 mm external:

### Environment

IP degree of protection	IP30
IK degree of protection	IK08
Standards	IS 8623-1 IS 8623-3 IEC 61439-3
Product certifications	CPRI ERDA

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.97 kg
Package 1 Height	7 cm
Package 1 width	31 cm
Package 1 Length	14.2 cm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>