

## Product data sheet

### Characteristics

# A9HMS210

Acti 9 - Metal P&S Unit - single door - 10A 1P  
+N+E 2Mod



### Main

Range	Acti 9
Product name	Metal Clad P&S Units
Product or component type	Consumer unit
Device application	Power socket distribution
Colour	White (RAL 9003)
Provided equipment	Electra plug and socket

### Complementary

Enclosure mounting	Flush Surface
[In] rated current	10 A
Poles description	1P + N + E
Total number of 18 mm modules	2
Enclosure/cubicle description	Single door enclosure
Enclosure material	Galvanized steel box Galvanized steel DIN rail Galvanized steel cable gland plate CRCA front plate
Height	170 mm external:
Width	150 mm external:
Depth	67 mm external:

### Environment

IP degree of protection	IP30
IK degree of protection	IK08
Standards	IS 8623-1 IS 8623-3 IEC 61439-3
Product certifications	CPRI ERDA

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.12 kg
Package 1 Height	7 cm
Package 1 width	17.6 cm
Package 1 Length	15.6 cm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>