

Product data sheet

Characteristics

MEH_VCGH1_050A44_3

MPP - CYL GH1 3PH 5KVA_r 440V 50Hz

Main

Range of product	VarPlus Can
Product or component type	Harmonic gas heavy duty capacitor

Complementary

Reactive power rating	5 kvar
Network rated voltage	440 V
Tuning factor	5.67 7
Maximum switching operation per year	7000
Diameter	63 mm
Height	195 mm
Quantity per set	1

Contractual warranty

Warranty	18 months
----------	-----------