



### Main

Range	Mureva
Product name	Mureva Enclosure
Product or component type	Weatherproof enclosure
Enclosure type	Mini enclosure for modular device
Mounting plate description	Without mounting plate

### Complementary

Enclosure mounting	Surface
9 mm pitches	8
Number of 18 mm modules per row	4
Total number of 18 mm modules	4
Number of horizontal rows	1
Electrical insulation class	Double insulation Class II
Provided equipment	1 marking kit 2 terminal block 4 holes
Type of front cover	Transparent
Power dissipation in W	10 W
[In] rated current	63 A
Type of rail	DIN
Number of pre-cutouts PG ISO	3
Number of terminal blocks	2 earth / neutral (screw connection) with 4 outgoing
Distribution block outgoing	4 x 10 mm <sup>2</sup> 4 x 16 mm <sup>2</sup>
Locking options description	Optional keylock
Enclosure material	Self-extinguishing polymer
Width	123 mm
Height	200 mm
Depth	112 mm
Internal depth	56 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Standards	EN 50262 IEC 60695-2-1 IEC 60670 IEC 61439-3
Fire resistance	650 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.000 cm
Package 1 Width	12.000 cm
Package 1 Length	20.000 cm
Package 1 Weight	515.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	9
Package 2 Height	22.500 cm
Package 2 Width	34.500 cm
Package 2 Length	41.000 cm
Package 2 Weight	4.950 kg
Unit Type of Package 3	P12
Number of Units in Package 3	216
Package 3 Height	80.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	139.200 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	25

## Contractual warranty

Warranty	18 months
----------	-----------