

Main

Device short name	MN
Product or component type	Voltage release
Device application	Control
Range compatibility	MasterPact NT ComPact NS630b...1600 ComPact NS1600b...3200 Masterpact NT NAVY Masterpact NW Masterpact NW NAVY
Voltage release type	Undervoltage release
[Uc] control circuit voltage	380...480 V AC 50/60 Hz

Complementary

Threshold tripping voltage	0.35...0.7 x Un opening 0.85 x Un closing
Supply holding power	4.5 VA
Mounting mode	Fixed
Response time	40 ms (Masterpact NT) 90 ms (Masterpact NW) 90 ms (Compact NS630b...1600) 90 ms (Compact NS1600b...3200)
Accessory / separate part category	Spare parts for Masterpact NT Spare parts for Masterpact NW Spare parts for Compact NS1600b...3200 Spare parts for Compact NS630b...1600

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	152 g
Package 1 Height	3.5 cm
Package 1 width	6.2 cm
Package 1 Length	8.2 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	1.568 kg
Package 2 Height	9 cm
Package 2 width	13.2 cm
Package 2 Length	18.5 cm
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Weight	19.243 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------