



Main

Product or component type	Auxiliary contact
Device short name	4 OF
Range compatibility	EasyPact MVS EasyPact EXE
Signal contacts composition	4 NO/NC



Complementary

Auxiliary contacts type	Standard
Mounting mode	Fixed
[Ie] rated operational current	AC-12: 10 A at 240/380 V AC 50/60 Hz AC-12: 10 A at 480 V AC 50/60 Hz AC-12: 6 A at 690 V AC 50/60 Hz DC-12: 10 A at 125 V DC DC-12: 3 A at 250 V DC
Minimum load	100 mA at 24 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	86.0 g
Package 1 Height	4.0 cm
Package 1 width	4.5 cm
Package 1 Length	7.0 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Weight	1.091 kg
Package 2 Height	9.0 cm
Package 2 width	15.0 cm
Package 2 Length	20.0 cm
Unit Type of Package 3	P12
Number of Units in Package 3	576
Package 3 Weight	66.768 kg
Package 3 Height	45.0 cm
Package 3 width	80.0 cm
Package 3 Length	120.0 cm

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Operations and descriptions

Operation	600
Duration of operation	4 min
Operation Description	Assembly and test

Contractual warranty

Warranty	18 months
----------	-----------