



Main

Range	Acti9
Product name	Flexi Tier
Product or component type	Consumer unit
Device application	Distribution
Colour	White (RAL 9003)
Provided equipment	Removable gland plates Removable centre plates Removable frame Grounding bar Neutral bar

Complementary

Enclosure mounting	Surface Flush
Number of horizontal rows	4
Number of 18 mm modules per row	10
Total number of 18 mm modules	40
Enclosure/cubicle description	Double door enclosure
Enclosure material	Galvanized steel box Galvanized steel chassis Galvanized steel cable gland plate Galvanized steel DIN rail CRCA door CRCA central plate CRCA frame
Door opening side	Reversible
Height	740.6 mm external:
Width	366 mm external:
Depth	101.6 mm external:

Environment

IP degree of protection	IP43
IK degree of protection	IK09
Standards	IS 8623-1 IS 8623-3 IEC 61439-3
Product certifications	CPRI[RETURN]ERDA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.8 cm
Package 1 Width	74.6 cm
Package 1 Length	37.2 cm
Package 1 Weight	14.09 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes