



### Main

Device application	Distribution
Range	Acti9
Product name	Acti9 K60
Product or component type	Miniature circuit-breaker
Device short name	K60H
Poles description	3P
Number of protected poles	3
[In] rated current	6 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	10000 A Icn at 415 V AC 50/60 Hz conforming to EN 60898-1 10000 A Icn at 415 V AC 50/60 Hz conforming to IEC 60898-1
Suitability for isolation	Yes
Standards	IEC 60898-1 EN 60898-1
Product certifications	ISI

### Complementary

Network frequency	50/60 Hz
Magnetic tripping limit	5...10 x In
[Ics] rated service breaking capacity	10 kA 75 % conforming to EN 60898-1 - 415 V AC 50/60 Hz 10 kA 75 % conforming to IEC 60898-1 - 415 V AC 50/60 Hz
Limitation class	3 conforming to EN 60898-1
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	4 kV
Contact position indicator	No
Control type	Toggle
Local signalling	Without
Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Downstream: biconnect
9 mm pitches	6
Height	81 mm
Width	54 mm
Depth	70 mm
Net weight	0.36 kg
Quantity per set	Set of 4
Colour	White
Mechanical durability	20000 cycles
Electrical durability	20000 cycles
Connections - terminals	Tunnel type terminals (downstream) 1...25 mm <sup>2</sup> rigid Tunnel type terminals (upstream) 1...25 mm <sup>2</sup> rigid Tunnel type terminals (downstream) 1...16 mm <sup>2</sup> flexible Tunnel type terminals (upstream) 1...16 mm <sup>2</sup> flexible
Wire stripping length	14 mm for top or bottom connection

Tightening torque	2 N.m top or bottom
Earth-leakage protection	Without

## Environment

IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	2 conforming to IEC 60898-1 2 conforming to EN 60898-1
Overvoltage category	II
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Operating altitude	0...2000 m
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-25...85 °C

## Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	5.0 cm
Package 1 Length	8.0 cm
Package 1 Weight	1.284 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free plastic parts & cables product