

# GS1AM2

Auxiliary contacts, TeSys GS, 2 C/O, early break, front mounting, for GS1 50-400 A with direct right handle



## Main

Range of product	TeSys
Device short name	GS1AM
Product or component type	Auxiliary contact
Contact application	O and I position signalling
Range compatibility	TeSys TeSys GS GS1 F fuse-switch disconnecter TeSys TeSys GS GS1G fuse-switch disconnecter TeSys TeSys GS GS1 J fuse-switch disconnecter TeSys TeSys GS GS1 K fuse-switch disconnecter TeSys TeSys GS GS1 L fuse-switch disconnecter TeSys TeSys GS GS1 N fuse-switch disconnecter TeSys TeSys GS GS1Q fuse-switch disconnecter
Contacts type and composition	2 C/O
Contact operation	Early-break
[Ith] conventional free air thermal current	16 A (at 40 °C)
[Ie] rated operational current	5 A at 127 V AC-15 4 A at 230 V AC-15 3 A at 400/415 V AC-15 2 A at 440 V AC-15 12 A at 24 V DC-13 2 A at 48 V DC-13 0.6 A at 110 V DC-13 0.4 A at 220 V DC-13

## Complementary

Mechanical durability	1 Mcycles
Electrical durability	30000 cycles AC-15
Switch rated current	50 A 63 A 100 A 125 A 160 A 200 A 250 A 315 A 400 A
Fuse type	NFC DIN BS
Type of operating handle	Direct right side
Mounting location	Front face
Net weight	0.035 kg

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	3.000 cm
Package 1 Length	10.000 cm
Package 1 Weight	39.000 g

Unit Type of Package 2	S01
Number of Units in Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	973.000 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

### Contractual warranty

Warranty	18 months
----------	-----------