

GV2APN01

Extended rotary handle kit, TeSys GV2, IP54, black handle, with trip indication, for GV2L-GV2P



Main

Range	TeSys TeSys Deca
Device short name	GV2AP
Product or component type	Rotary handle kit
Accessory / separate part category	Control accessory
Handle colour	Black
Handle front plate colour	Grey

Complementary

Product compatibility	GV2P GV2L
Rotary handle padlocking	Padlock in OFF position Padlock in ON position
Rotary handle mounting style	Extended
Locking options description	1 to 3 padlocks
Back/door distance	140...250 mm
Net weight	0.2 kg

Environment

IP degree of protection	IP54
-------------------------	------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	37 cm
Package 1 Length	9 cm
Package 1 Weight	362 g
Unit Type of Package 2	Doboz
Number of Units in Package 2	12
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.728 kg
Unit Type of Package 3	P06
Number of Units in Package 3	96
Package 3 Height	75 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	50.492 kg


Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins


Contractual warranty

Warranty	18 months
----------	-----------

Mounting of External Operator GV2APN01, GV2APN02 or GV2APN04 for Motor Circuit Breakers GV2L



Door cut-out



(1) For IP65 only.