

Main

| | |
|--|---|
| Range | Linergy |
| Product name | FT |
| Device short name | GV2G |
| Product or component type | Comb busbar |
| Accessory / separate part category | Connection accessory |
| Poles description | 3P |
| Range compatibility | TeSys Deca TeSys GV2 TeSys K TeSys U |
| Number of tap-offs | 4 |
| [I _{th}] conventional free air thermal current | 63 A |
| Connection pitch | 45 mm |

Complementary

| | |
|-------------------------------|-------------|
| Mounting location | On terminal |
| [Ui] rated insulation voltage | 690 V |
| Length | 179 mm |
| Net weight | 0.077 kg |

Packing Units

| | |
|------------------------------|------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.000 cm |
| Package 1 Width | 3.500 cm |
| Package 1 Length | 18.000 cm |
| Package 1 Weight | 78.000 g |
| Unit Type of Package 2 | S01 |
| Number of Units in Package 2 | 60 |
| Package 2 Height | 15.000 cm |
| Package 2 Width | 15.000 cm |
| Package 2 Length | 40.000 cm |
| Package 2 Weight | 4.930 kg |
| Unit Type of Package 3 | P06 |
| Number of Units in Package 3 | 1920 |
| Package 3 Height | 75.000 cm |
| Package 3 Width | 60.000 cm |
| Package 3 Length | 80.000 cm |
| Package 3 Weight | 165.460 kg |

Offer Sustainability

| | |
|--|---|
| Packaging without single use plastic | No |
| Packaging made with recycled cardboard | No |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| Take-back | No |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|