

Main

Range	Easy TeSys
Range of product	Easy TeSys Control
Product or component type	Contacteur coil
Device short name	LAEX
Product compatibility	LC1E32...E38
Accessory / separate part category	Spare parts
Control circuit type	AC at 50/60 Hz standard
[Uc] control circuit voltage	220 V AC 50/60 Hz
Average resistance	509.7 Ohm at 20 °C
Inductance of closed circuit	17.72 H

Complementary

Control circuit voltage limits	Operational: 0.85...1.1 Uc at 50/60 Hz (at <55 °C)
Inrush power in VA	70 VA 50/60 Hz cos phi 0.75 (at 20 °C)
Hold-in power consumption in VA	7 VA 50 Hz cos phi 0.3 (at 20 °C) 7.5 VA 60 Hz cos phi 0.3 (at 20 °C)






Environment

Ambient air temperature for operation	-5...55 °C
Net weight	0.073 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	6.2 cm
Package 1 Length	7.8 cm
Package 1 Weight	65.6 g

Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	Yes
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No
