



Main

Product or component type	Circuit breaker
Device short name	Compact NSX400
Circuit breaker name	Compact NSX400
Device application	Distribution
Poles description	4P
Breaking capacity code	F
Trip unit name	MicroLogic 6.3 A
Trip unit technology	Electronic
Trip unit rating	400 A

Complementary

Network frequency	50 Hz
Control type	Toggle
Mounting mode	Fixed
[In] rated current	400 A at 40 °C
[Ui] rated insulation voltage	800 V 50 Hz
[Ue] rated operational voltage	690 V 50/60 Hz
Breaking capacity	36 kA Icu
[Ics] rated service breaking capacity	36 kA
Connection pitch	45 mm

Environment

IP degree of protection	IP40 conforming to IEC 60947-2
IK degree of protection	IK07 conforming to IEC 62262

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.6 cm
Package 1 Width	19.95 cm
Package 1 Length	29.1 cm
Package 1 Weight	8.31 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------