



Main

Range of product	PowerLogic
Product or component type	Heavy duty capacitor
Device application	PFC equipment assembly

Complementary

Reactive power rating	3 kvar
Rated voltage	440 V
[In] rated current	3.9 A
Network frequency	50 Hz
Capacitance tolerance	- 5 % to 10 %
[Imp] maximum permanent current	1.8 x Is
Inrush current	Up to 250 x In
Service life in hours	130000 h
Impregnation material	Bio-degradable PUR resin Non-PCB
Operating altitude	4000 m
Safety function	Discharge device Pressure sensitive disconnecter for every phase Self healing
Fixing mode	Threaded M12 stud at bottom
Diameter	50 mm
Height	245 mm
Net weight	0.6 kg

Environment

Standards	IS 13340-1993 IEC 60831-1/2 IS 13341-1992
IP degree of protection	IP20
Relative humidity	0...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	28.5 cm
Package 1 Width	11.0 cm
Package 1 Length	27.0 cm
Package 1 Weight	900.0 g
Unit Type of Package 2	S03

Number of Units in Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	10800.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile