



Main

Range of product	PowerLogic
Product or component type	Standard duty capacitor
Device application	PFC equipment assembly

Complementary

Reactive power rating	15 kvar
Rated voltage	440 V
[In] rated current	19.4 A
Network frequency	50 Hz
Capacitance tolerance	- 5 % to 10 %
[Imp] maximum permanent current	1.5 x Is
Inrush current	Up to 200 x In
Service life in hours	100000 h
Impregnation material	Non-PCB Bio-degradable PUR resin
Operating altitude	4000 m
Safety function	Self healing Pressure sensitive disconnecter for every phase Discharge device
Fixing mode	Threaded M12 stud at bottom
Diameter	75 mm
Height	308 mm
Net weight	1.2 kg

Environment

Standards	IS 13340-1993 IEC 60831-1/2 IS 13341-1992
IP degree of protection	IP20
Relative humidity	0...95 %

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	35.0 cm
Package 1 Width	13.0 cm
Package 1 Length	13.0 cm
Package 1 Weight	1.61 kg
Unit Type of Package 2	S04
Number of Units in Package 2	8

Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	12.88 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information