



Main

Range of product	VarPlus Can
Product or component type	Standard duty capacitor
Device application	PFC equipment assembly

Complementary

Reactive power rating	25 kvar
Rated voltage	440 V
[In] rated current	32.8 A
Network frequency	50 Hz
Capacitance tolerance	- 5 % to 10 %
[Imp] maximum permanent current	1.5 x Is
Inrush current	Up to 200 x In
Service life in hours	100000 h
Impregnation material	Non-PCB Bio-degradable PUR resin
Operating altitude	4000 m
Safety function	Discharge device Pressure sensitive disconnecter for every phase Self healing
Fixing mode	Threaded M12 stud at bottom
Diameter	90 mm
Height	308 mm
Net weight	2.4 kg

Environment

Standards	IEC 60831-1/2 IS 13341-1992 IS 13340-1993
IP degree of protection	IP20
Relative humidity	0...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.61 kg
Package 1 Height	35 cm
Package 1 width	13 cm
Package 1 Length	13 cm
Unit Type of Package 2	S04
Number of Units in Package 2	8

Package 2 Weight	20.88 kg
Package 2 Height	30 cm
Package 2 width	40 cm
Package 2 Length	60 cm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration