



## Main

Range of product	PowerLogic
Product or component type	Standard duty capacitor
Device application	PFC equipment assembly

## Complementary

Reactive power rating	25 kvar
Rated voltage	440 V
[In] rated current	32.8 A
Network frequency	50 Hz
Capacitance tolerance	- 5 % to 10 %
[Imp] maximum permanent current	1.5 x Is
Inrush current	Up to 200 x In
Service life in hours	100000 h
Impregnation material	Non-PCB Bio-degradable PUR resin
Operating altitude	4000 m
Safety function	Discharge device Pressure sensitive disconnecter for every phase Self healing
Fixing mode	Threaded M12 stud at bottom
Diameter	90 mm
Height	308 mm
Net weight	2.4 kg

## Environment

Standards	IEC 60831-1/2 IS 13341-1992 IS 13340-1993
IP degree of protection	IP20
Relative humidity	0...95 %

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	35.0 cm
Package 1 Width	13.0 cm
Package 1 Length	13.0 cm
Package 1 Weight	2.61 kg
Unit Type of Package 2	S04

Number of Units in Package 2	8
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	20.88 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>