

Main

Range of product	Jeevan D-Start
Device short name	7MDL
Product or component type	Enclosed automatic DOL starter
Motor starter composition	With contactor + overload relay + socket and plug
Thermal protection adjustment range	13...18 A
Motor power kW	2.25 kW, 240 V AC, single phase
Motor power hp	3 hp, 240 V AC, single phase
Control type	Padlocking facility ON/OFF push-button
Locking options description	Padlock in OFF position
Device application	Individual motor compensation

Complementary

Motor starter type	Direct on line
Protection type	Overload protection Built into each single phase element
Fuse type	32 A HRC fuse Rewirable fuse 19 SWG
Enclosure material	Sheet metal
Surface finish	Powder coated
Width	154 mm
Height	184 mm
Depth	110 mm
Maximum number of switchings	100000 operations
Operating rate	40 operations/hour

Environment

Environmental characteristic	Dust and vermin resistant
------------------------------	---------------------------

Contractual warranty

Warranty	18 months
----------	-----------