

Main

Range	Livia
Product or component type	Socket-outlet
Device application	Power supply
Net weight	34 kg
Number of modules	2
Colour tint	White (RAL 9003)
Targeted channel	Do it yourself

Complementary

Device presentation	Mechanism with central plate
Fixing mode	Snap-fitted
Device mounting	Flush
Outlet poles configuration	2P + E with shutter
Rated current	6 A at 250 V AC 50 Hz
Socket additional information	Shuttered
Connections - terminals	By screw solid or flexible
Material	PC
Cover type	Flush cover
Signalling function	Without
Resistance to chemical agents	Not resistant to alcohols Not resistant to cleaning agent Not resistant to thinner
Surface treatment	Antibacterial
Surface finish	Glossy
Number of terminals	3
Embedding depth	28.7 mm

Environment

Standards	IS 1293
Ambient air temperature for operation	-5...35 °C
IP degree of protection	IP20
Depth	35.25 mm
Width	45.2 mm
Height	54.4 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.4 cm
Package 1 Width	6.2 cm
Package 1 Length	7.8 cm
Package 1 Weight	40 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	6.8 cm
Package 2 Width	10.8 cm
Package 2 Length	22 cm
Package 2 Weight	400 g
Unit Type of Package 3	CAR
Number of Units in Package 3	300
Package 3 Height	34.2 cm
Package 3 Width	36 cm
Package 3 Length	45.6 cm
Package 3 Weight	12.88 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
SCIP Number	B4bb8a57-d202-4769-a2e0-19cfa1805b08
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	3