



### Main

Range of product	Easy Modicon M200
Product or component type	Analogue output cartridge
Product compatibility	Easy Modicon M200

### Complementary

Analogue output number	2
Analogue output type	Voltage: 0...10 V
Analogue output resolution	12 bits
LSB value	2.44 mV 0...10 V voltage
Load type	Resistive
Load impedance ohmic	$\geq 2 \text{ k}\Omega$
Conversion time	20 ms
Stabilisation time	40 ms
Absolute accuracy error	+/- 1 % of full scale +/- 0.3 % of full scale at 25 °C
Temperature drift	+/- 0.02 %FS/°C
Repeat accuracy	+/- 0.4 %FS
Non-linearity	+/- 0.01 %FS
Cross talk	$\leq 1 \text{ LSB}$
Type of cable	Twisted shielded pairs cable
Electrical connection	3 x 1.5 mm <sup>2</sup> 2 screw terminal blocks with pitch 3.81 mm adjustment for outputs
Maximum cable distance between devices	Twisted shielded pairs cable: <30 m for output
Insulation	Non-insulated between analogue output and internal logic
Height	41 mm
Depth	15 mm
Width	35 mm
Net weight	0.012 kg

### Environment

Immunity to microbreaks	10 ms
-------------------------	-------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	7.0 cm
Package 1 Length	3.5 cm
Package 1 Weight	20.0 g
Unit Type of Package 2	S02

Number of Units in Package 2	75
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.07 kg
Unit Type of Package 3	P06
Number of Units in Package 3	1200
Package 3 Height	75 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	106 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>