



Main

Range of product	Altivar
Range compatibility	Altivar 312 Altivar 61 Altivar Lift Altivar 32 Altivar Machine ATV320 Altivar 312 Solar Altivar 212 Altivar 71 Altivar 61Q Altivar 71Q
Accessory / separate part category	Display and signalling accessories
Accessory / separate part type	Display terminal
Accessory / separate part destination	Variable speed drive
Product specific application	To control, adjust and configure the drive To save and download configurations To display the current values
IP degree of protection	IP54

Complementary

Mounting location	On the door of an enclosure
User language	Italian English French Spanish German Chinese
Messages display capacity	8 lines
Pixel resolution	240 x 160
Net weight	0.145 kg

Environment

Ambient air temperature for operation	-15...50 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	275 g
Package 1 Height	7 cm
Package 1 width	16.5 cm
Package 1 Length	23 cm
Unit Type of Package 2	P06
Number of Units in Package 2	56
Package 2 Weight	28.42 kg
Package 2 Height	77 cm
Package 2 width	80 cm
Package 2 Length	60 cm
Unit Type of Package 3	S03

Number of Units in Package 3	7
Package 3 Weight	2.413 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------