



Main

| | |
|-----------------------------|--|
| Product or component type | Communication card |
| Range compatibility | Altivar 71 Altivar 61Q Altivar 61 Altivar 71Q |
| Communication port protocol | Profibus DP |
| Connector type | 9-way female SUB-D connector |
| Transmission rate | 1.5 Mbps 12 Mbps 9600 bps 3 Mbps 500 kbps 19.2 kbps 187.5 kbps 6 Mbps 93.75 kbps |

Complementary

| | |
|-----------------------|---|
| Number of addresses | 1...126 |
| Communication service | CiA 402 profile I/O profile I/O data Communication monitoring can be inhibited, adjustable PPO type 5 |
| Display type | 1 LED for DX (data exchange) 1 LED for ST (status) Graphic display terminal for control word received Graphic display terminal for I/O data Graphic display terminal for reference received |
| Net weight | 0.3 kg |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 7.200 cm |
| Package 1 Width | 17.000 cm |
| Package 1 Length | 23.000 cm |
| Package 1 Weight | 281.000 g |
| Unit Type of Package 2 | S03 |
| Number of Units in Package 2 | 7 |
| Package 2 Height | 30.000 cm |
| Package 2 Width | 30.000 cm |
| Package 2 Length | 40.000 cm |
| Package 2 Weight | 2.512 kg |
| Unit Type of Package 3 | P06 |
| Number of Units in Package 3 | 56 |
| Package 3 Height | 75.000 cm |
| Package 3 Width | 60.000 cm |
| Package 3 Length | 80.000 cm |
| Package 3 Weight | 30.388 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|