

# XVGM2S

Monolithic tower lights, Easy Harmony XVG, 60mm, red green, steady light, buzzer, aluminium tube mounting and L bracket, IP23, 220...240V AC

## Main

Range of product	Easy Harmony XVG
Product or component type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	2 illuminated units
Material	PC (UL94 V-2): globe
Mounting diameter	60 mm
Component name	XVG
Device mounting	Tube with L bracket
Light source	LED steady
Light block color	Red/green
Indicator bank base type	Base with integrated buzzer

## Complementary

Rated supply voltage	220...240 V AC
Cable cross section	0.33 mm <sup>2</sup>
Discrete output type	PNP
[Uimp] rated impulse withstand voltage	4.0 kV
Current consumption	55 mA
Noise level	85 dB
Power consumption in VA	8.7 VA
Fundamental frequency	2.64 kHz
Net weight	0.48 kg

## Environment

Product certifications	CE[RETURN]CCC[RETURN]EAC
Ambient air temperature for storage	-20...65 °C
Ambient air temperature for operation	0...50 °C
Electrical shock protection class	Class I
Overvoltage category	III conforming to IEC 60947-5-1
IP degree of protection	IP23

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.500 cm
Package 1 Width	13.500 cm
Package 1 Length	56.500 cm
Package 1 Weight	712.000 g
Unit Type of Package 2	P06
Number of Units in Package 2	30
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm

Package 2 Length	80.000 cm
Package 2 Weight	31.310 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No