



Oversikt

Presentasjon	APC Metered by Outlet with Switching Rack Power Distribution Units (PDUs) enable advanced, user-customizable power control and individual outlet power metering. Remote outlet level controls allow power on/off functionality for power recycling to reboot locked-up equipment and to avoid unauthorized use of individual outlets. Power sequencing delays allow users to define the order in which to power up or down attached equipment. Avoid circuit overload during power recovery and extend uptime of critical equipment by prioritizing the load shedding. Current metering provides real-time remote monitoring of connected loads. Switched Rack PDUs include real power monitoring, a temperature/humidity sensor port, and locking IEC receptacles. User-defined alarms warn of potential circuit overloads before critical IT failures occur. Users can access, configure, and control Switched rack PDUs through secure Web, SNMP, or Telnet Interfaces and is complimented by APC Centralized Management platforms using InfraStruxure Central, Capacity Manager and Change Manager.
Leveringstid	Usually in Stock

Teknisk informasjon

Farge	Sort
Produkt eller type komponent	PDU
PDU type	Metered outlet
Cord length	3,00 m
Antall kabler	1
Tilgjengelig utstyr	CAN port terminator Installation guide Rack mounting brackets Safety guide Serial configuration cable

Komplementær

Input Voltage	200 V 208 V 230 V
Høyde	182,9 cm
Bredde	5,6 cm
Output Voltage	230 V
Dybde	5,1 cm
Vekt	8,23 kg
Montasjeplassering	Side
Mounting preference	No preference
Input Plug Type	IEC 60309 32 A 2P + E
Monteringsmetode	Rack-mounted
Rack units	0U
USB kompatibel	No
Monteringsposisjon	Vertikal
Tillatt spenning	220...240 V
Maksimal linjestrøm	32 A

Inngangsstrøms grenser	32 A
Load capacity	7400 VA
Nettverksfrekvens	50/60 Hz
Outlet type and quantity	21 IEC 60320 C13 3 IEC 60320 C19

Miljø

Produktsertifikater	VDE
Standarder	EN 55022 klasse A EN 55024 EN 61000-3-2 EN 61000-3-3
Omgivelsestemperatur drift	-5...60 °C
Relativ fuktighet	5...95 %
Driftshøyde	0...10000 ft
Omgivelsestemperatur for lagring	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0,00...15240,00 m

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	203,8 cm
Pakke 1 Bredde	16,2 cm
Pakke 1 Vekt	11,8 cm
Package 1 Weight	10,5 kg

Bærekraftig

Produktets miljøstatus	Green Premium miljømerket produkt
REACH-regelverk	 REACH-erklæring
EU RoHS-direktiv	Samsvar med unntak
Blyfri	Ja
Kvikksølvfri	Ja
Informasjon om RoHS-unntak	 Ja
Miljøinformasjon	 Produktmiljøprofil
Produktets livssyklus	 Informasjon Om Levetidsslutt
WEEE	Innen EU må produktet avhendes i henhold til bestemte regler for avfallshåndtering og aldri kastes som husholdningsavfall.
Optimalisert energieffektivitet	Energieffektivt produkt
Take-back	Take-back program available

Logistisk informasjon

Opprinnelsesland	IN
------------------	----

Garantiperiode

Garanti	2 years repair or replace
---------	---------------------------