



Oversikt

Presentasjon	This Series of Rack Power Distribution Units (PDU) comes with Locking IEC Receptacles. The output and input connections are C13 to C14. The cord length is 1.8m. Locking IEC system allows the use of optional locking IEC power cords for added power cord security and enhanced reliability. No tools are required to disengage the locking feature and remove the plug from the locking receptacle.
Leveringstid	Usually in Stock

Teknisk informasjon

Produkt eller type komponent	Power cord
Input Connection Type	IEC 60320 C14
Kabellengde	1,83 m
Antall kabler	6

Fysisk

Farge	Sort
Høyde	24 cm
Bredde	7,5 cm
Dybde	5,5 cm
Vekt	1,35 kg
Mounting preference	No preference
Monteringsmetode	Not rack-mountable

Inngang

Maksimal linjestrøm	10 A
Inngangsstrøms grenser	10 A

Utgang

Max current draw	10 A
Antall strømuttak	1 IEC 60320 C13
Kabellengde	1,83 m

Overenstemmelse

Produktsertifikater	CCC[RETURN]PSE[RETURN]VDE
---------------------	---------------------------

Miljømessig

Omgivelsestemperatur drift	0...70 °C
Relativ fuktighet	20...80 %
Driftshøyde	0...10000 ft
Omgivelsestemperatur for lagring	-25...75 °C
Storage Relative Humidity	20...80 %
Storage altitude	0,00...15240,00 m

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	24 cm
Pakke 1 Bredde	5,5 cm
Pakke 1 Vekt	7,5 cm
Package 1 Weight	1,35 kg

Bærekraftig

Produktets miljøstatus	Green Premium miljømerket produkt
REACH-regelverk	 REACH-erklæring
EU RoHS-direktiv	I samsvar  EU RoHS-erklæring
Blyfri	Ja
Miljøinformasjon	 Produktmiljøprofil
Produktets livssyklus	 Informasjon Om Levetidsslutt
WEEE	Innen EU må produktet avhendes i henhold til bestemte regler for avfallshåndtering og aldri kastes som husholdningsavfall.
Take-back	Take-back program available

Garantiperiode

Garanti	2 years repair or replace
---------	---------------------------