



Oversikt

Presentasjon	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Leveringstid	Usually in Stock

Teknisk informasjon

Produkt eller type komponent	Power cord
Input Connection Type	IEC 60320 C20
Kabellengde	1,83 m
Antall kabler	6

Fysisk

Farge	Sort
Høyde	30 cm
Bredde	8 cm
Dybde	7 cm
Vekt	2,16 kg
Mounting preference	No preference
Monteringsmetode	Not rack-mountable

Inngang

Maksimal linjestrøm	16 A
Inngangsstrøms grenser	16 A

Utgang

Max current draw	16 A
Antall strømuttak	1 IEC 60320 C19
Kabellengde	1,83 m

Overenstemmelse

Produktsertifikater	CCC[RETURN]CSA[RETURN]PSE[RETURN]UL listet[RETURN]VDE
---------------------	---

Miljømessig

Omgivelsestemperatur drift	0...75 °C
Relativ fuktighet	20...80 %
Driftshøyde	0...10000 ft
Omgivelsestemperatur for lagring	-25...75 °C
Storage Relative Humidity	20...80 %
Storage altitude	0,00...15240,00 m

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	30 cm
Pakke 1 Bredde	8 cm
Pakke 1 Vekt	7 cm
Package 1 Weight	2,16 kg
SCC14	10731304279720

Bærekraftig

Produktets miljøstatus	Green Premium miljømerket produkt
REACH-regelverk	 REACH-erklæring
EU RoHS-direktiv	I samsvar  EU RoHS-erklæring
Blyfri	Ja
Miljøinformasjon	 Produktmiljøprofil
Produktets livssyklus	 Informasjon Om Levetidsslutt
WEEE	Innen EU må produktet avhendes i henhold til bestemte regler for avfallshåndtering og aldri kastes som husholdningsavfall.
Take-back	Take-back program available

Logistisk informasjon

Opprinnelsesland	CN
------------------	----

Garantiperiode

Garanti	2 years repair or replace
---------	---------------------------