



Oversikt

Presentasjon	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Leveringstid	Usually in Stock

Teknisk informasjon

Input Connection Type	IEC 60309 16 A 2P + E
Kabellengde	3,00 m

Fysisk

Høyde	43,2 cm
Bredde	15,2 cm
Dybde	10,2 cm
Vekt	0,49 kg
Mounting preference	No preference
Monteringsmetode	Not rack-mountable

Inngang

Maksimal linjestrøm	16 A
Inngangsstrøms grenser	16 A

Utgang

Max current draw	16 A
Antall strømuttak	1 IEC 60320 C19
Kabellengde	3,05 m

Overenstemmelse

Produktsertifikater	VDE
---------------------	-----

Miljømessig

Omgivelsestemperatur drift	0...70 °C
Relativ fuktighet	20...80 %
Driftshøyde	0...10000 ft
Omgivelsestemperatur for lagring	-25...70 °C
Storage Relative Humidity	20...80 %
Storage altitude	0,00...15240,00 m

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	43,2 cm
Pakke 1 Bredde	15,2 cm
Pakke 1 Vekt	10,2 cm
Package 1 Weight	0,49 kg

Bærekraftig

Produktets miljøstatus	Green Premium miljømerket produkt
REACH-regelverk	REACH-erklæring
EU RoHS-direktiv	I samsvar EU RoHS-erklæring
Blyfri	Ja
Miljøinformasjon	Produktmiljøprofil
Produktets livssyklus	Informasjon Om Levetidsslutt
WEEE	Innen EU må produktet avhendes i henhold til bestemte regler for avfallshåndtering og aldri kastes som husholdningsavfall.
Take-back	Take-back program available

Logistisk informasjon

Opprinnelsesland	CN
------------------	----

Garantiperiode

Garanti	2 years repair or replace
---------	---------------------------