



Oversikt

Presentasjon

APC Metered Rack Power Distribution Units (PDUs) provide active metering to enable energy optimization and circuit protection. User-defined alarm thresholds mitigate risk with real-time local and remote alerts to warn of potential circuit overloads. Metered Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership. Metered Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers. Users can access and configure Metered Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency.

Leveringstid

Usually in Stock

Teknisk informasjon

Farge	Sort
PDU type	Metered
Cord length	3,00 m
Antall kabler	1
Tilgjengelig utstyr	Installation guide Locking input power cord Rack mounting brackets Serial configuration cable Safety guide

Komplementær

Input Voltage	200 V 208 V 230 V
Høyde	90,2 cm
Bredde	5,6 cm
Output Voltage	230 V
Dybde	4,4 cm
Vekt	2,93 kg
Montasjeplassering	Side
Mounting preference	No preference
Input Plug Type	IEC 60309 16 A 2P + E
Monteringsmetode	Rack-mounted
Rack units	0U
Monteringsposisjon	Vertikal
Tillatt spenning	100...240 V
Maksimal linjestrøm	16 A
Inngangsstrøms grenser	16 A
Load capacity	3700 VA
Nettverksfrekvens	50/60 Hz
Outlet type and quantity	18 IEC 60320 C13 2 IEC 60320 C19

Miljø

Produktsertifikater	METI Denan[RETURN]VDE
Standarder	CSA C22.2 No 60950 IEC 60950 UL 60950-1
Omgivelsestemperatur drift	-5...60 °C
Relativ fuktighet	5...95 %
Driftshøyde	0...10000 ft
Omgivelsestemperatur for lagring	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0,00...15240,00 m

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	112,4 cm
Pakke 1 Bredde	16,2 cm
Pakke 1 Vekt	10,7 cm
Package 1 Weight	4,91 kg

Bærekraftig

Produktets miljøstatus	Green Premium miljømerket produkt
REACH-regelverk	 REACH-erklæring
EU RoHS-direktiv	Samsvar med unntak
Blyfri	Ja
Kvikksølvfri	Ja
Informasjon om RoHS-unntak	 Ja
Miljøinformasjon	 Produktmiljøprofil
Produktets livssyklus	 Informasjon Om Levetidsslutt
WEEE	Innen EU må produktet avhendes i henhold til bestemte regler for avfallshåndtering og aldri kastes som husholdningsavfall.
Optimalisert energieffektivitet	Energieffektivt produkt
Take-back	Take-back program available

Logistisk informasjon

Opprinnelsesland	IN
------------------	----

Garantiperiode

Garanti	2 years repair or replace
---------	---------------------------