



Oversikt

Presentasjon	APC Metered Rack Power Distribution Units (PDUs) provide active metering to enable energy optimization and circuit protection. User-defined alarm thresholds mitigate risk with real-time local and remote alerts to warn of potential circuit overloads. Metered Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership. Metered Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers. Users can access and configure Metered Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency.
Leveringstid	Usually in Stock

Teknisk informasjon

Farge	Sort
Produkt eller type komponent	PDU
PDU type	Metered
Cord length	1,83 m
Antall kabler	1
Tilgjengelig utstyr	Installation guide Rack mounting brackets Serial configuration cable Safety guide

Komplementær

Input Voltage	400 V 3 faser
Høyde	182,9 cm
Bredde	5,6 cm
Output Voltage	240 V
Dybde	5,1 cm
Vekt	9,6 kg
Montasjeplassering	Side
Mounting preference	No preference
Input Plug Type	IEC 60309 30 A 3P + N + E
Monteringsmetode	Not rack-mountable
Rack units	0U
Monteringsposisjon	Vertikal
[in] merkestrøm	24 A
Maksimal linjestrøm	30 A
Inngangsstrøms grenser	30 A
Load capacity	17300 VA
Nettverksfrekvens	50/60 Hz
Outlet type and quantity	30 IEC 60320 C13 12 IEC 60320 C19

Miljø

Produktsertifikater	cUL listed[RETURN]UL listet[RETURN]VCCI klasse A
Standarder	EN 55022 klasse A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC part 15 class A ICES-003
Omgivelsestemperatur drift	-5...60 °C
Relativ fuktighet	5...95 %
Driftshøyde	0...10000 ft
Omgivelsestemperatur for lagring	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0,00...15240,00 m

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	214,9 cm
Pakke 1 Bredde	11,2 cm
Pakke 1 Vekt	22,1 cm
Package 1 Weight	13,6 kg

Bærekraftig

Produktets miljøstatus	Green Premium miljømerket produkt
REACH-regelverk	 REACH-erklæring
EU RoHS-direktiv	Samsvar med unntak
Blyfri	Ja
Kvikksølvfri	Ja
Informasjon om RoHS-unntak	 Ja
Miljøinformasjon	 Produktmiljøprofil
Produktets livssyklus	 Informasjon Om Levetidsslutt
Optimalisert energieffektivitet	Energieffektivt produkt
Take-back	Take-back program available

Garantiperiode

Garanti	2 years repair or replace
---------	---------------------------