



Oversikt

Presentasjon	Wide and Deep Universal IT enclosure with increased enclosure width for more cable management options in denser server and networking applications. Includes integrated vertical 1U mounting spaces adjacent the enclosures standard EIA-310 equipment mounting u-spaces that can be removed and replaced with 1U accessories. Enclosures are deep to provide additional equipment clearance space or more open space for ease of access in the rear of the enclosure. 42U height to easily roll through doorways.
Leveringstid	Usually in Stock

Teknisk informasjon

Produkt eller type komponent	Rack enclosure
Antall rack-enhet	42U
Inkludert utstyr	Baying hardware Doors Key(S) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters 4 x bolt down brackets Roof Side panels Unpacking sheet

Fysisk

Høyde	205,7 cm
Bredde	80 cm
Dybde	120 cm
Vekt	139,5 kg
Farge	Sort
Mounting preference	No preference
Monteringsmetode	Not rack-mountable
Maks monteringsdybde	91,69 cm
Minimum monteringsdybde	16,76 cm
Rack width	19"
Merking	14 gauge EIA mounting rail 16 gauge front door 18 gauge post 16 gauge rear door 19 gauge roof 18 gauge side panels
Permanent tillatt belastning	459,94 Kg dynamisk 1000,17 kg statisk

Overenstemmelse

Standarder	UL 2416 UL 60950-1 EIA-310E
------------	-----------------------------------

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	218,1 cm
Pakke 1 Bredde	94 cm
Pakke 1 Vekt	130 cm
Package 1 Weight	160,064 kg

Bærekraftig

Produktets miljøstatus	Green Premium miljømerket produkt
REACH-regelverk	REACH-erklæring
REACH fri for SVHC	Ja
EU RoHS-direktiv	Proaktivt i samsvar (Produktet inngår ikke i EUs RoHS direktivet) EU RoHS-erklæring
Fri for giftige tungmetaller	Ja
Kvikksølvfri	Ja
Informasjon om RoHS-unntak	Ja
Miljøinformasjon	Produktmiljøprofil
Take-back	Take-back program available

Garantiperiode

Garanti	5 year repair or replace
---------	--------------------------