



Teknisk informasjon

Produktspekter	Harmony XVU
Produkt eller type komponent	Modular tower light
Sjømærke eller indikator bank enhetstype	LED unit
Montasjediameter	60 mm
Type komponent	XVU
Lyskilde	LED, Rød
Applikasjon	Automotive Pakkemaskin Maskinverktøy

Komplementær

Signaltype	Blinkende
Monteringsmåte	Kunde montering, opp til 5 enheter Opptil 4 enheter med summer
Materiale	PC (polykarbonat) V-2 flammehemmende i samsvar med UL 94 PC (polykarbonat) V-0 flammehemmende i samsvar med UL 94
[Us] matespenning	24 V AC/DC
Maksimalt effekttap i w	0,9 W
Signaltype	Blinkende
Lengde	50 mm
Vekt	0,064 kg

Miljø

Produktsertifikater	CE[RETURN]UL[RETURN]CSA
Omgivelsestemperatur for lagring	-40...70 °C
IP-grad	IP65
Omgivelsestemperatur drift	-25...50 °C
Vibrasjonsmotstand	2 gn

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	9,0 cm
Pakke 1 Bredde	9,2 cm
Pakke 1 Vekt	13,1 cm
Package 1 Weight	146,0 g
Enhetstype pakke 2	S03
Antall enheter i pakke 2	24
Pakke 2 Høyde	30 cm
Pakke 2 Bredde	30 cm
Pakke 2 Lengde	40 cm
Pakke 2 Vekt	4,353 kg
Enhetstype pakke 3	P06
Antall enheter i pakke 3	192
Pakke 3 Høyde	75 cm

Pakke 3 Bredde	60 cm
Pakke 3 Lengde	80 cm
Pakke 3 Vekt	41 kg

Bærekraftig

Produktets miljøstatus	Green Premium miljømerket produkt
REACH-regelverk	 REACH-erklæring
EU RoHS-direktiv	Proaktivt i samsvar (Produktet inngår ikke i EUs RoHS direktivet)
Kvikksølvfri	Ja
Kinas RoHS-forskrift	 Kinas RoHS-Erklæring
Informasjon om RoHS-unntak	 Ja
Miljøinformasjon	 Produktmiljøprofil
Produktets livssyklus	 Informasjon Om Levetidsslutt

Logistisk informasjon

Opprinnelsesland	ID
------------------	----


Garantiperiode

Garanti	18 måneder
---------	------------


Illuminated LED Unit

Dimensions

mm
in.




Modular Tower Lights Mounting



Drawing	Part number	Part name
A1	-	Top cover
-	Top cover (Silver)	
A2	XVUC9S	Buzzer unit
XVUC9SQ	Buzzer unit (Silver)	
A3	XVUC23	Green LED unit
XVUC24	Red LED unit	
XVUC25	Orange LED unit	
XVUC26	Blue LED unit	
XVUC27	White LED unit	
XVUC28	Yellow LED unit	
A4	XVUC29	Multi-LED unit
A5	XVUC29P	Multi-LED unit, Pulse signal
A6	XVUC9V	Sound unit
A7	XVUC9VP	Sound unit, Pulse signal
A8	XVUC020	Extender
XVUC020Q	Extender (Silver)	
A9	XVUC21B	DC body

Drawing	Part number	Part name
XVUC21BQ	DC body (Silver)	
A10	XVUC21M	AC body NPN
XVUC21MP	AC body PNP	
XVUC21MQP	AC body PNP (Silver)	
A11	XVUZ06	Flexible option
A12	XVUZ01	Fixing Unit - Direct mounting (3 pins)
XVUZ01Q	Fixing Unit - Direct mounting (Silver,3 pins)	
XVUZ03	Fixing Unit - Direct mounting (2 pins)	
XVUZ04	Fixing Unit - Direct mounting (4 pins)	
A13	XVUZ02	Fixing Unit - Plate with Pole (100 mm)
XVUZ02Q	Fixing Unit - Plate with Pole (100 mm, Silver)	
XVUZ400	Fixing Unit - Plate with Pole (400 mm)	
XVUZ800	Fixing Unit - Plate with Pole (800 mm)	
A14	XVUZ05	Fixing Unit - Plate with adjustment pole (100-385 mm)
A15	XVUC43	Green LED unit, Flash
XVUC44	Red LED unit, Flash	
XVUC45	Orange LED unit, Flash	
XVUC46	Blue LED unit, Flash	
XVUC47	White LED unit, Flash	
XVUC48	Yellow LED unit, Flash	
A16	XVUZ100T	Fixing Unit - Metal bracket with pole (100 mm)
XVUZ250T	Fixing Unit - Metal bracket with pole(250 mm)	
XVUZ400T	Fixing Unit - Metal bracket with pole (400 mm)	
A17	XVUZ12	Fixing plate for use on vertical support - black

Illuminated Units, Multi-LED and Audible Units Wiring



- (A) Fixing Unit
- (1) Dimensions of Wiring size
- (2) Push-in Wire Connectors
- (3) Fuse : 2A ,250V
- (4) Fuse : 0.5A ,125V
- (5) Modular Tower Lights 24V AC/DC
- (6) Modular Tower Lights 100...240V AC
- L1 to Illuminated LED Units
- L5 :