

Teknisk informasjon

Produktspekter	Harmony XVU
Produkt eller type komponent	Modular tower light
Tilbehør / type del	Justerbar pol
Tilbehør / separat del kategori	Montering og innfesting tilbehør
Type komponent	XVU
Montasjediameter	60 mm

Komplementær

Pol høyde	210...385 mm
Montering	Plate with adjustable pole
Kompatibilitet	Topp: DC body
Materiale	PBT (polybutylene terephthalate) V-0 flammehemmende i samsvar med UL 94 ABS (Akrylnitril-Butadien-Styren) PC (polykarbonat) Aluminium
Farge på kapsling	Svart
Tilkoblinger	Push-in
[Us] matespenning	24 V AC/DC
Lengde	209,7...384,7 mm
Vekt	0,253 kg

Miljø

Omgivelsestemperatur for lagring	-40...70 °C
Omgivelsestemperatur drift	-25...50 °C
IP-grad	IP65
Produktsertifikater	UL[RETURN]CE[RETURN]CSA

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	9,1 cm
Pakke 1 Bredde	26,8 cm
Pakke 1 Vekt	9,0 cm
Package 1 Weight	420,0 g
Enhetstype pakke 2	S03
Antall enheter i pakke 2	12
Pakke 2 Høyde	30,0 cm
Pakke 2 Bredde	30,0 cm
Pakke 2 Lengde	40,0 cm
Pakke 2 Vekt	5,963 kg
Enhetstype pakke 3	PAL
Antall enheter i pakke 3	96
Pakke 3 Høyde	60,0 cm

Pakke 3 Bredde	80,0 cm
Pakke 3 Lengde	70,0 cm
Pakke 3 Vekt	48,32 kg

Bærekraftig

Produktets miljøstatus	Green Premium miljømerket produkt
REACH-regelverk	 REACH-erklæring
EU RoHS-direktiv	Proaktivt i samsvar (Produktet inngår ikke i EUs RoHS direktivet)
Kvikksølvfri	Ja
Kinas RoHS-forskrift	 Kinas RoHS-Erklæring
Informasjon om RoHS-unntak	 Ja
Miljøinformasjon	 Produktmiljøprofil
Produktets livssyklus	 Informasjon Om Levetidsslutt

Logistisk informasjon


Opprinnelsesland	ID
------------------	----

Garantiperiode

Garanti	18 måneder
---------	------------


Fixing Unit - Plate with Adjustable Pole

Dimensions



(1) adjustment: 209.7 ... 384.7 or adjustment: 8.256 ... 15.146

Modular Tower Lights Mounting



Drawing	Part number	Part name
A1	-	Top cover
-	Top cover (Silver)	
A2	XVUC9S	Buzzer unit
XVUC9SQ	Buzzer unit (Silver)	
A3	XVUC23	Green LED unit
XVUC24	Red LED unit	
XVUC25	Orange LED unit	
XVUC26	Blue LED unit	
XVUC27	White LED unit	
XVUC28	Yellow LED unit	
A4	XVUC29	Multi-LED unit
A5	XVUC29P	Multi-LED unit, Pulse signal
A6	XVUC9V	Sound unit
A7	XVUC9VP	Sound unit, Pulse signal
A8	XVUC020	Extender
XVUC020Q	Extender (Silver)	
A9	XVUC21B	DC body

Drawing	Part number	Part name
XVUC21BQ	DC body (Silver)	
A10	XVUC21M	AC body NPN
XVUC21MP	AC body PNP	
XVUC21MQP	AC body PNP (Silver)	
A11	XVUZ06	Flexible option
A12	XVUZ01	Fixing Unit - Direct mounting (3 pins)
XVUZ01Q	Fixing Unit - Direct mounting (Silver,3 pins)	
XVUZ03	Fixing Unit - Direct mounting (2 pins)	
XVUZ04	Fixing Unit - Direct mounting (4 pins)	
A13	XVUZ02	Fixing Unit - Plate with Pole (100 mm)
XVUZ02Q	Fixing Unit - Plate with Pole (100 mm, Silver)	
XVUZ400	Fixing Unit - Plate with Pole (400 mm)	
XVUZ800	Fixing Unit - Plate with Pole (800 mm)	
A14	XVUZ05	Fixing Unit - Plate with adjustment pole (100-385 mm)
A15	XVUC43	Green LED unit, Flash
XVUC44	Red LED unit, Flash	
XVUC45	Orange LED unit, Flash	
XVUC46	Blue LED unit, Flash	
XVUC47	White LED unit, Flash	
XVUC48	Yellow LED unit, Flash	
A16	XVUZ100T	Fixing Unit - Metal bracket with pole (100 mm)
XVUZ250T	Fixing Unit - Metal bracket with pole(250 mm)	
XVUZ400T	Fixing Unit - Metal bracket with pole (400 mm)	
A17	XVUZ12	Fixing plate for use on vertical support - black

Illuminated Units, Multi-LED and Audible Units Wiring



- (A) Fixing Unit
- (1) Dimensions of Wiring size
- (2) Push-in Wire Connectors
- (3) Fuse : 2A ,250V
- (4) Fuse : 0.5A ,125V
- (5) Modular Tower Lights 24V AC/DC
- (6) Modular Tower Lights 100...240V AC
- L1 to Illuminated LED Units
- L5 :