



Osnovne informacije

Tip proizvoda ili komponente	Pomoćni kontakt
Kratko ime uređaja	OF[RETURN]SD[RETURN]SDE[RETURN]SDV
Primena uređaja	Nadzor statusa prekidača
Kompatibilnost grupe proizvoda	Compact Compact NS630b...1600 Compact Compact NS1600b...3200 Compact Compact INS Compact Compact INV Compact Compact NSX EasyPact EasyPact CVS PowerPact PowerPact Multistandard Compact Compact NSX DC
Sastav signalnih kontakata	1 NO/NC

Dopunske informacije

Tip greške	Opšti električni kvar
Lokalna signalizacija	Zaotvori/Zatvori: ON/OFF očitavanje Zaindikator okidanja releja: indikator okidanja Zaelektrična greška: Fault trip
Tip pomoćnog kontakta	Standardni
Način montiranja	Sistemom na klik
[ith] dozvoljena termička struja u vazduhu	5 A
Breaking capacity (A)	AC-12: 6 A at 24 V AC 50/60 Hz AC-12: 6 A at 48 V AC 50/60 Hz AC-12: 6 A at 110 V AC 50/60 Hz AC-12: 6 A at 220/240 V AC 50/60 Hz AC-12: 6 A at 380/440 V AC 50/60 Hz AC-12: 6 A at 480 V AC 50/60 Hz AC-12: 6 A at 660/690 V AC 50/60 Hz AC-15: 6 A at 24 V AC 50/60 Hz AC-15: 6 A at 48 V AC 50/60 Hz AC-15: 5 A at 110 V AC 50/60 Hz AC-15: 4 A at 220/240 V AC 50/60 Hz AC-15: 2 A at 380/440 V AC 50/60 Hz AC-15: 1,5 A at 480 V AC 50/60 Hz AC-15: 0,1 A at 660/690 V AC 50/60 Hz DC-12: 6 A at 24 V DC 50/60 Hz DC-12: 2,5 A at 48 V DC 50/60 Hz DC-12: 0,6 A at 110 V DC 50/60 Hz DC-12: 0,3 A at 250 V DC 50/60 Hz DC-14: 1 A at 24 V DC 50/60 Hz DC-14: 0,2 A at 48 V DC DC-14: 0,05 A at 110 V DC DC-14: 0,03 A at 250 V DC
Minimalno opterećenje	100 mA pri 24 V DC
Pomoćni priključni blok	Opruga 0,5...1,5 mm ² (AWG 20...AWG 16)
Pribor / posebna kategorija	Rezervni deo za Compact NS630b...1600 Rezervni deo za Compact NS1600b...3200

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1,400 cm
Package 1 Width	7,000 cm
Package 1 Length	7,000 cm
Package 1 Weight	16,900 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4,500 cm
Package 2 Width	16,000 cm
Package 2 Length	16,000 cm
Package 2 Weight	177,000 g
Unit Type of Package 3	S03
Number of Units in Package 3	300
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	5,785 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Bez PVC	Da
Učinak u vezi sa sadržajem halogena	Proizvod sa plastičnim delovima bez halogena

Ugovorna garancija

Garancija	18 meseci
-----------	-----------