



Osnovne informacije

Primena uređaja	Razvod električne energije
Grupa proizvoda	Acti 9
Ime proizvoda	Acti 9 iC60
Tip proizvoda ili komponente	Minijaturni prekidač
Kratko ime uređaja	iC60N
Broj polova	2P
Broj zaštićenih polova	2
[in] nazivna struja	32 A
Tip mreže	DC AC
Tehnologija zaštitne jedinice	Termomagnetna
Kod krive	C
Prekidna moć	6000 A Icn pri 400 V AC 50/60 Hz u skladu sa EN/IEC 60898-1 36 KA Icu pri 12...60 V AC 50/60 Hz u skladu sa EN/IEC 60947-2 10 KA Icu pri ≤ 125 V DC u skladu sa EN/IEC 60947-2 10 KA Icu pri 380...415 V AC 50/60 Hz u skladu sa EN/IEC 60947-2 20 KA Icu pri 220...240 V AC 50/60 Hz u skladu sa EN/IEC 60947-2 6 KA Icu pri 440 V AC 50/60 Hz u skladu sa EN/IEC 60947-2 36 KA Icu pri 100...133 V AC 50/60 Hz u skladu sa EN/IEC 60947-2
Kategorija upotrebe	Kategorija A u skladu sa EN 60947-2 Kategorija A u skladu sa IEC 60947-2
Pogodno za izolaciju	Da u skladu sa EN 60898-1 Da u skladu sa EN 60947-2 Da u skladu sa IEC 60898-1 Da u skladu sa IEC 60947-2
Standardi	EN 60898-1 EN 60947-2 IEC 60947-2 IEC 60898-1

Dopunske informacije

Mrežna frekvencija	50/60 Hz
Ograničenje prekostrujne zaštite	8 x In +/- 20 %
[ics] servisna prekidna moć	15 KA 75 % u skladu sa EN 60947-2 - 220...240 V AC 50/60 Hz 7,5 KA 75 % u skladu sa EN 60947-2 - 380...415 V AC 50/60 Hz 4,5 KA 75 % u skladu sa EN 60947-2 - 440 V AC 50/60 Hz 15 KA 75 % u skladu sa IEC 60947-2 - 220...240 V AC 50/60 Hz 7,5 KA 75 % u skladu sa IEC 60947-2 - 380...415 V AC 50/60 Hz 4,5 KA 75 % u skladu sa IEC 60947-2 - 440 V AC 50/60 Hz 27 KA 75 % u skladu sa IEC 60947-2 - 12...133 V AC 50/60 Hz 27 KA 75 % u skladu sa EN 60947-2 - 12...133 V AC 50/60 Hz 6000 A 100 % u skladu sa EN 60898-1 - 400 V AC 50/60 Hz 6000 A 100 % u skladu sa IEC 60898-1 - 400 V AC 50/60 Hz 10 KA 100 % u skladu sa IEC 60947-2 - 72...125 V DC 10 kA 100 % u skladu sa EN 60947-2 - 72...125 V DC
Klasa limitacije	3 u skladu sa EN 60898-1 3 u skladu sa IEC 60898-1
[ui] nazivni napon izolacije	500 V AC 50/60 Hz u skladu sa EN 60947-2 500 V AC 50/60 Hz u skladu sa IEC 60947-2
[uimp] nazivni podnosivi impulsni napon	6 kV u skladu sa EN 60947-2 6 kV u skladu sa IEC 60947-2
Indikator pozicije kontakta	Da
Tip upravljanja	Ručica
Lokalna signalizacija	Indikator okidanja
Način montiranja	Fiksno
Nosači za montažu	DIN šina
Razvodni blok češljaste sabirnice	Gornji ili donji: DA
9 mm redovi	4
Visina	85 mm
Širina	36 mm
Dubina	78,5 mm
Masa proizvoda	0,25 kg
Boja	Bela
Mehanička trajnost	20000 ciklusa
Električna trajnost	10000 ciklusa
Povezivanje - priključci	Pojedinačni priključni blok (gornji ili donji) 1...35 mm ² kruti Pojedinačni priključni blok (gornji ili donji) 1...25 mm ² fleksibilni
Dužina ogoljenog dela žice	14 mm for gornji ili donji connection
Moment pritezanja	3,5 N.m gornji ili donji
Diferencijalna zaštita	Poseban blok

Okruženje

Ip stepen zaštite	IP20 conforming to IEC 60529 IP20 conforming to EN 60529
Stepen zaprljanosti	3 u skladu sa EN 60947-2 3 u skladu sa IEC 60947-2
Kategorija prenapona	IV
Tropikalizacija	2 u skladu sa IEC 60068-1
Relativna vlažnost	95 % pri 55 °C
Nadmorska visina za rad	EcoStruxure EV Charging Expert
Temperatura okoline za rad uređaja	-35...70 °C
Temperatura okoline za skladištenje	-40...85 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,500 cm
Package 1 Width	7,500 cm
Package 1 Length	9,500 cm

Package 1 Weight	238,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	8,000 cm
Package 2 Width	10,000 cm
Package 2 Length	22,500 cm
Package 2 Weight	1,489 kg
Unit Type of Package 3	S03
Number of Units in Package 3	66
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	16,769 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
EU RoHS direktiva	У складу са изузецима
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Učinak u vezi sa sadržajem halogena	Proizvod bez halogena

Ugovorna garancija

Garancija	18 meseci
-----------	-----------