



### Osnovne informacije

|                                          |                                        |
|------------------------------------------|----------------------------------------|
| Grupa proizvoda                          | Acti 9                                 |
| Ime proizvoda                            | Acti 9 iID                             |
| Tip proizvoda ili komponente             | Prekidač diferencijalne zaštite (RCCB) |
| Kratko ime uređaja                       | iID                                    |
| Broj polova                              | 2P                                     |
| Pozicija nultog provodnika               | Levo                                   |
| [in] nazivna struja                      | 25 A                                   |
| Tip mreže                                | AC                                     |
| Osetljivost diferencijalne zaštite       | 500 mA                                 |
| Kašnjenje prorade diferencijalne zaštite | Trenutna                               |
| Klasa diferencijalne zaštite             | Tip AC                                 |

### Dopunske informacije

|                                            |                                                                                                                                                                                                                                                                          |
|--------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Lokacija uređaja u sistemu                 | Izvod                                                                                                                                                                                                                                                                    |
| Mrežna frekvencija                         | 50/60 Hz                                                                                                                                                                                                                                                                 |
| [ue] nazivni napon                         | 220...240 V AC 50/60 Hz                                                                                                                                                                                                                                                  |
| Tehnologija prorade diferencijalne zaštite | Nezavisna                                                                                                                                                                                                                                                                |
| Nazivna moć uključenja i isključenja       | Idm 1500 A<br>Im 1500 A                                                                                                                                                                                                                                                  |
| Nazivna uslovna struja kratkog spoja       | 10 kA                                                                                                                                                                                                                                                                    |
| [ui] nazivni napon izolacije               | 500 V AC 50/60 Hz                                                                                                                                                                                                                                                        |
| [uimp] nazivni podnosivi impulsni napon    | 6 kV                                                                                                                                                                                                                                                                     |
| Udarna struja                              | 250 A                                                                                                                                                                                                                                                                    |
| Indikator pozicije kontakta                | Da                                                                                                                                                                                                                                                                       |
| Tip upravljanja                            | Ručica                                                                                                                                                                                                                                                                   |
| Način montiranja                           | Sistemom na klik                                                                                                                                                                                                                                                         |
| Nosači za montažu                          | DIN šina                                                                                                                                                                                                                                                                 |
| 9 mm redovi                                | 4                                                                                                                                                                                                                                                                        |
| Visina                                     | 91 mm                                                                                                                                                                                                                                                                    |
| Širina                                     | 36 mm                                                                                                                                                                                                                                                                    |
| Dubina                                     | 73,5 mm                                                                                                                                                                                                                                                                  |
| Masa proizvoda                             | 0,21 kg                                                                                                                                                                                                                                                                  |
| Boja                                       | Bela                                                                                                                                                                                                                                                                     |
| Mehanička trajnost                         | 20000 ciklusa                                                                                                                                                                                                                                                            |
| Električna trajnost                        | AC-1: 15000 ciklusa                                                                                                                                                                                                                                                      |
| Opis opcija zaključavanja                  | Uređaj za zaključavanje                                                                                                                                                                                                                                                  |
| Povezivanje - priključci                   | Pojedinačni priključni blok gornji ili donji 1...35 mm <sup>2</sup> kruti<br>Pojedinačni priključni blok gornji ili donji 1...25 mm <sup>2</sup> fleksibilni<br>Pojedinačni priključni blok gornji ili donji 1...25 mm <sup>2</sup> fleksibilni sa kablovskim završetkom |
| Dužina ogoljenog dela žice                 | 14 mm for gornji ili donji connection                                                                                                                                                                                                                                    |
| Moment pritezanja                          | 3,5 N.m gornji ili donji                                                                                                                                                                                                                                                 |

## Okruženje

|                                     |                                                                                |
|-------------------------------------|--------------------------------------------------------------------------------|
| Standardi                           | EN/IEC 61008-1                                                                 |
| Ip stepen zaštite                   | IP20 conforming to IEC 60529<br>IP40 (modularni orman) conforming to IEC 60529 |
| Stepen zaprljanosti                 | 3                                                                              |
| Elektromagnetna kompatibilnost      | 8/20 µs podnosivi strujni impuls, 250 A u skladu sa EN/IEC 61008-1             |
| Temperatura okoline za rad          | -5...60 °C                                                                     |
| Temperatura okoline za skladištenje | -40...85 °C                                                                    |

## Pakovanje

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 4,0 cm     |
| Package 1 Width              | 8,5 cm     |
| Package 1 Length             | 10,0 cm    |
| Package 1 Weight             | 205 g      |
| Unit Type of Package 2       | S03        |
| Number of Units in Package 2 | 54         |
| Package 2 Height             | 30,0 cm    |
| Package 2 Width              | 30,0 cm    |
| Package 2 Length             | 40,0 cm    |
| Package 2 Weight             | 11,511 kg  |
| Unit Type of Package 3       | P12        |
| Number of Units in Package 3 | 432        |
| Package 3 Height             | 44,4 cm    |
| Package 3 Width              | 80 cm      |
| Package 3 Length             | 120 cm     |
| Package 3 Weight             | 104,088 kg |

## Održivost ponude

|                                     |                                                                                                                                                                             |
|-------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Status održive ponude               | Green Premium proizvod                                                                                                                                                      |
| Propis REACH                        |  <a href="#">REACH Deklaracija</a>                                                       |
| EU RoHS direktiva                   | U skladu sa izuzecima                                                                                                                                                       |
| Bez žive                            | Da                                                                                                                                                                          |
| RoHS regulativa za Kinu             |  <a href="#">RoHS Deklaracija Za Kinu</a>                                                |
| Informacije o RoHS izuzecima        |  <a href="#">Da</a>                                                                      |
| Izjava o zaštiti okoliša            |  <a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>                               |
| Profil cirkularnosti                | Nema potrebe za namenskim operacijama recikliranja                                                                                                                          |
| WEEE                                | Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke. |
| Učinak u vezi sa sadržajem halogena | Proizvod sa plastičnim delovima bez halogena                                                                                                                                |

## Ugovorna garancija

|           |           |
|-----------|-----------|
| Garancija | 18 meseci |
|-----------|-----------|