



Osnovne informacije

Grupa proizvoda	Acti9
Ime proizvoda	Acti 9 iSW
Tip proizvoda ili komponente	Rastavljač
Kratko ime uređaja	iSW
Primena uređaja	Upravljanje
Broj polova	3P
Kategorija upotrebe	AC-22A
Pogodno za izolaciju	Da

Dopunske informacije

[ie] nazivna struja	32 A pri 415 V AC 50/60 Hz
[ue] nazivni napon	415 V AC 50/60 Hz
[ui] nazivni napon izolacije	500 V AC 50/60 Hz u skladu sa EN/IEC 60669-2-4
[uimp] nazivni podnosivi impulsni napon	4 kV
Tip upravljanja	Ručica
Lokalna signalizacija	ON/OFF očitavanje
Indikator pozicije kontakta	Da
Način montiranja	Fiksno
Nosači za montažu	DIN šina
9 mm redovi	4
Visina	77 mm
Širina	36 mm
Dubina	70 mm
Boja	Bela
Mehanička trajnost	300000 ciklusa
Električna trajnost	30000 ciklusa
Povezivanje - priključci	Tunelski priključci - 10 mm ² - kruti Tunelski priključci - 10 mm ² - fleksibilni Tunelski priključci - 10 mm ² - fleksibilni sa kablovskim završetkom
Dužina ogoljenog dela žice	9 mm
Moment pritezanja	1,2 N.m

Okruženje

Standardi	EN/IEC 60669-2-4
Ip stepen zaštite	IP4
Stepen zaprljanosti	2
Tropikalizacija	2
Relativna vlažnost	95 % pri 55 °C
Temperatura okoline za rad uređaja	-20...50 °C
Temperatura okoline za skladištenje	-40...70 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,5 cm
Package 1 Width	7,5 cm
Package 1 Length	8,5 cm
Package 1 Weight	117,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	8,5 cm
Package 2 Width	9,5 cm
Package 2 Length	22,0 cm
Package 2 Weight	751,41 g
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	9,452 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------