



Osnovne informacije

Grupa proizvoda	Ultra
Tip proizvoda ili komponente	Podna kanalica
Nijansa boje	Siva (RAL 7023)
Količina po setu	40 m

Dopunske informacije

Materijal parapetnog razvoda	Plastika
Podela odeljaka	4 odeljka
Dimenzije parapetnog razvoda	77 x 19 mm
Materijal	PVC (polivinil-hlorid)
Dužina	2000 mm
Visina	19 mm
Širina	77 mm

Okruženje

Standardi	EN 50085-1:2005 EN 50085-2-1:2006
Temperatura okoline za rad uređaja	-15...60 °C
Ip stepen zaštite	IP40
Ik stepen zaštite	IK07

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,0 cm
Package 1 Width	3,0 cm
Package 1 Length	200,0 cm
Package 1 Weight	439,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	88
Package 2 Height	14,0 cm
Package 2 Width	35,0 cm
Package 2 Length	200,0 cm
Package 2 Weight	19,341 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------