



Osnovne informacije

Grupa proizvoda	TeSys TeSys Deca
Kratko ime uređaja	GVAM
Tip proizvoda ili komponente	Pomoćni kontakti blok
Kompatibilnost proizvoda	GV2L GV2ME GV2RT GV3L GV2P GV3P GV2LE
Kompatibilnost grupe proizvoda	TeSys TeSys GV3 GV3P prekidač TeSys GV3 GV3L prekidač
Lokacija za montiranje	Leva strana
Operacije pomoćnih kontakata	Signal kratkog spoja 1 C/O
Raspored kontakata	1 C/O

Dopunske informacije

[ui] nazivni napon izolacije	690 V u skladu sa IEC 60947-1 300 V u skladu sa UL 508 300 V u skladu sa CSA C22.2 No 14
[ue] nazivni radni napon	24...240 V AC 24...60 V DC
[ith] dozvoljena termička struja u vazduhu	2,5 A for signal greške
Mehanička trajnost	100000 ciklusa
Minimalna struja preklapanja	5 mA
Minimalni napon preklapanja	17 V
Tip zaštite	GB2CB... prekidač GG osigurač 10 A
Nazivna snaga u va	36 VA pri 24 V AC-14 - električna trajnost: 1000 ciklusa pri 1,5 A 48 VA pri 48 V AC-14 - električna trajnost: 1000 ciklusa pri 1 A 72 VA pri 110...127 V AC-14 - električna trajnost: 1000 ciklusa pri 0,5 A 72 VA pri 230...240 V AC-14 - električna trajnost: 1000 ciklusa pri 0,3 A
Nazivna snaga u w	120 W pri 240 V DC-13 - električna trajnost: 100000 ciklusa 140 W pri 110 V DC-13 - električna trajnost: 100000 ciklusa 140 W pri 24 V DC-13 - električna trajnost: 100000 ciklusa 180 W pri 60 V DC-13 - električna trajnost: 100000 ciklusa 240 W pri 48 V DC-13 - električna trajnost: 100000 ciklusa 15 W pri 48 V DC-13 - električna trajnost: 1000 ciklusa 24 W pri 24 V DC-13 - električna trajnost: 1000 ciklusa 9 W pri 60 V DC-13 - električna trajnost: 1000 ciklusa
Moment pritezanja	1,4 N.m - na vijčani priključni blokovi
Visina	89 mm
Širina	9,3 mm
Dubina	66 mm
Masa proizvoda	0,055 kg
Boja	Tamnosiva

Okruženje

Karakteristike životne sredine	Normalna sredina
Sertifikacija proizvoda	UKCA

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1,5 cm
Package 1 Width	7,0 cm
Package 1 Length	9,0 cm
Package 1 Weight	39 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	10,0 cm
Package 2 Width	10,5 cm
Package 2 Length	15,3 cm
Package 2 Weight	440 g
Unit Type of Package 3	S02
Number of Units in Package 3	60
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2,944 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------