



Osnovne informacije

Grupa proizvoda	OptiLine 45
Kablovski instalacioni sistem	Parapetni razvod
Tip proizvoda ili komponente	Instalacija kablovskih kanalic
Nijansa boje	Polarno bela (RAL 9003)
Količina po setu	12 m

Dopunske informacije

Materijal parapetnog razvoda	Plastika
Dimenzije parapetnog razvoda	95 x 55 mm
Podela odeljaka	1 odeljak
Lokacija za montiranje	Interna
Način pričvršćivanja	Sa zavrtnjima bez matice
Veličina otvora sa prednje strane	45 mm
Materijal	PVC (polivinil-hlorid)
Dužina	2000 mm
Visina	95 mm
Širina	55 mm

Okruženje

Standardi	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002 NF C 68-102
Temperatura okoline za rad uređaja	-25...60 °C
Ip stepen zaštite	IP40
Ik stepen zaštite	IK07

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	2
Package 1 Height	5,5 cm
Package 1 Width	9,5 cm
Package 1 Length	200,0 cm
Package 1 Weight	2,01 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	12,5 cm
Package 2 Width	28,5 cm
Package 2 Length	204,0 cm
Package 2 Weight	12,31 kg

Unit Type of Package 3	PAL
Number of Units in Package 3	192
Package 3 Height	64,0 cm
Package 3 Width	120,0 cm
Package 3 Length	210,0 cm
Package 3 Weight	217,0 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja