



Osnovne informacije

Grupa proizvoda	OptiLine 70 OptiLine 45
Kablovski instalacioni sistem	Parapetni razvod
Product type	Krajnja kapa
Colour	Polarno bela (RAL 9003)
Quantity package 1 / unit	Set od 2

Dopunske informacije

Materijal parapetnog razvoda	Plastika
Dimenzije parapetnog razvoda	95 x 55 mm
Način pričvršćivanja	Zatvaranje sa klikom Zavrtnjem
Product material	PC/ABS
Dužina	21 mm
Visina	99 mm
Širina	56 mm

Okruženje

Standardi	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1
Operating temperature	-25...60 °C
Ip stepen zaštite	IP40
Ik stepen zaštite	IK07

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,2 cm
Package 1 Width	5,8 cm
Package 1 Length	10,0 cm
Package 1 Weight	25,0 g
Unit Type of Package 2	BAG
Number of Units in Package 2	2
Package 2 Height	3,0 cm
Package 2 Width	6,0 cm
Package 2 Length	11,0 cm
Package 2 Weight	53,0 g
Unit Type of Package 3	S03

Number of Units in Package 3	200
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	5,843 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja