



Osnovne informacije

Kablovski instalacioni sistem	Podne kutije
Product type	Unica podna kutija
Tip poda	Dupli pod Pod sa šupljinama Betonski pod
Oblik podne kutije	Pravougaona
Colour	Siva (RAL 7011)
Quantity package 1 / unit	1 deo

Dopunske informacije

Broj modula	8 modula
Product material	Čelik PA6 PBT (polibutilen-tereftalat)
Dužina	199 mm
Visina	72 mm
Širina	276 mm

Okruženje

Standardi	73/23/EEC 93/68/EEC IEC 61084-1:ed. 1, 1991 IEC 61084-2-2:2003
Operating temperature	-25...60 °C
Ip stepen zaštite	IP20

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8,5 cm
Package 1 Width	21,5 cm
Package 1 Length	29,0 cm
Package 1 Weight	1,495 kg
Unit Type of Package 2	P12
Number of Units in Package 2	120
Package 2 Height	112,0 cm
Package 2 Width	80,0 cm
Package 2 Length	120,0 cm
Package 2 Weight	190,44 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------