

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ili navedenih informacija.

Moment pritezanja	1,7 N.M - sa odvijačem matica Ø 6 mm 1,7 N.M - sa odvijačem Philips No 2 1,7 N.m - sa odvijačem pozidiv broj 2
Visina	48 mm
Širina	44 mm
Dubina	61 mm
Boja	Tamnosiva

Okruženje

Karakteristike životne sredine	Normalna sredina
Ip stepen zaštite	IP20 conforming to IEC 60529
Zaštitni tretman	TH u skladu sa IEC 60068
Temperatura okoline za skladištenje	-60...80 °C
Temperatura okoline za rad uređaja	-40...70 °C
Nadmorska visina za rad uređaja	3000 m

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,200 cm
Package 1 Width	6,500 cm
Package 1 Length	5,000 cm
Package 1 Weight	74,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5,200 cm
Package 2 Width	13,000 cm
Package 2 Length	24,000 cm
Package 2 Weight	756,000 g
Unit Type of Package 3	S03
Number of Units in Package 3	140
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	11,121 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	У складу са изузецима
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Bez PVC	Da

Ugovorna garancija

Garancija	18 meseci
-----------	-----------