



Osnovne informacije

Grupa proizvoda	TeSys
Ime proizvoda	TeSys LE
Kratko ime uređaja	LE1M
Tip proizvoda ili komponente	DOL starter u kućištu
Primena uređaja	Standardno
Kategorija upotrebe	AC-3
Sastav uređaja	Kontaktor Priključni blok uzemljenja Priključni blok nultog provodnika Releji termičkog preopterećenja
Podešavanje termičkog preopterećenja	3,7...5,5 A
Snaga motora kw	0,75 KW pri 240 V AC 50/60 Hz 2,2 KW pri 415 V AC 50/60 Hz 1,1 KW pri 220/230 V AC 50/60 Hz 2,2 kW pri 380/400 V AC 50/60 Hz
[Uc] control circuit voltage	380 V AC 50/60 Hz
Način upravljanja	Taster start zelena I Taster stop/reset crvena O

Dopunske informacije

Lokalna signalizacija	U radu: LED (žuta)
Broj kablovskih uvoda	2 kablovski uvod: ISO20 vrh 2 kablovski uvod: ISO25 vrh 2 kablovski uvod: Pg 13 vrh 2 kablovski uvod: Pg 21 vrh 2 kablovski uvod: ISO20 dno 2 kablovski uvod: ISO25 dno 2 kablovski uvod: Pg 13 dno 2 kablovski uvod: Pg 21 dno 2 kablovski uvod: Pg 16 vrh 2 kablovski uvod: Pg 16 dno
Širina	78 mm
Visina	160 mm
Dubina	108 mm
Masa proizvoda	0,6 kg

Okruženje

Materijal	ABS (akrilonitril-butadien-stiren)
Ip stepen zaštite	IP65 u skladu sa IEC 60529
Standardi	IEC 60947-4-1
Temperatura okoline za rad	-5...40 °C
Karakteristike životne sredine	Standardna sredina
Sertifikacija proizvoda	UKCA

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11,600 cm
Package 1 Width	16,600 cm
Package 1 Length	8,200 cm
Package 1 Weight	572,900 g
Unit Type of Package 2	S02
Number of Units in Package 2	6
Package 2 Height	15,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	3,766 kg
Unit Type of Package 3	P06
Number of Units in Package 3	96
Package 3 Height	75,000 cm
Package 3 Width	60,000 cm
Package 3 Length	80,000 cm
Package 3 Weight	70,788 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------