



Osnovne informacije

Grupa proizvoda	Resi9
Ime proizvoda	Resi9 MP
Tip proizvoda ili komponente	Orman
Tip ormana	Modularni orman
Nb of 18 mm modules per row	12
Nb of horizontal rows	2
Type of door	Dimovani
Širina	Spoljašnja strana: 268 mm
Visina	Spoljašnja strana: 353 mm
Dubina	Spoljašnja strana : 102 mm

Dopunske informacije

Montaža ormana	Površinska
9 mm redovi	24
Ukupan broj 18 mm modula	24
[in] nazivna struja	63 A
Tip šine	35 mm asimetrična šina
Opis montažne ploče	Bez montažne ploče
Funkcija priključnog bloka	Uzemljenje/nula
Broj priključnih blokova	1 uzemljenje (vijčano) sa 16 izvodi 1 nula (vijčano) sa 16 izvodi
Izvodi razvodnog bloka	2 x 16 mm ² za uzemljenje 2 x 16 mm ² za nula 6 x 6 mm ² za uzemljenje 6 x 6 mm ² za nula 8 x 10 mm ² za uzemljenje 8 x 10 mm ² za nula
Materijal kućišta	Zadnji deo: tehno plastika Vrata: tehno plastika Prednja strana: tehno plastika
Unutrašnja dubina	80 mm
Boja	Prednja strana: bela (RAL 9003) Vrata: dimovana
Segment tržišta	Stambene zgrade Male komercijalne zgrade

Okruženje

Standardi	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Oznake kvaliteta	IMQ
Otpornost na vatru	Vrata: 650 °C Zadnji deo: 650 °C Prednja strana: 650 °C
Ip stepen zaštite	IP40
Ik stepen zaštite	IK07
Temperatura okoline za rad uređaja	-25...60 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10,500 cm
Package 1 Width	27,000 cm
Package 1 Length	33,500 cm
Package 1 Weight	1,205 kg
Unit Type of Package 2	S04
Number of Units in Package 2	5
Package 2 Height	30,000 cm
Package 2 Width	40,000 cm
Package 2 Length	60,000 cm
Package 2 Weight	6,937 kg
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	120,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	122,992 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Učinak u vezi sa sadržajem halogena	Proizvod bez halogena

Ugovorna garancija

Garancija	18 meseci
-----------	-----------