



Osnovne informacije

Grupa proizvoda	Resi9
Ime proizvoda	Resi9 MP
Tip proizvoda ili komponente	Orman
Tip ormana	Modularni orman
Nb of 18 mm modules per row	12
Nb of horizontal rows	3
Type of door	Zatamnjeni
Širina	Zid: 270 mm Spoljašnja strana: 294 mm
Visina	Zid: 478 mm Spoljašnja strana: 502 mm
Dubina	Spoljašnja strana : 18 mm Zid : 80 mm Ukupno : 98 mm

Dopunske informacije

Montaža ormana	Ugradna
9 mm redovi	24
Ukupan broj 18 mm modula	36
[in] nazivna struja	63 A
Tip šine	35 mm asimetrična šina
Opis montažne ploče	Bez montažne ploče
Kablovski uvod	Predefinisani otvori
Funkcija priključnog bloka	Uzemljenje/nula
Broj priključnih blokova	1 uzemljenje (vijčano) sa 20 izvodi 1 nula (vijčano) sa 20 izvodi
Izvodi razvodnog bloka	2 x 16 mm ² za uzemljenje 2 x 16 mm ² za nula 9 x 10 mm ² za uzemljenje 9 x 10 mm ² za nula 9 x 6 mm ² za uzemljenje 9 x 6 mm ² za nula
Materijal kućišta	Zadnji deo: tehno plastika Vrata: tehno plastika Prednja strana: tehno plastika
Unutrašnja dubina	76 mm
Boja	Prednja strana: bela (RAL 9003) Vrata: zatamnjena (RAL 9003)
Segment tržišta	Stambene zgrade Male komercijalne zgrade

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova društva ili zavisna društva neće snositi odgovornost za zloupotrebu ovenavedenih informacija.

Okruženje

Standardi	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Oznake kvaliteta	IMQ
Otpornost na vatru	Vrata: 650 °C Zadnji deo: 650 °C Prednja strana: 650 °C
Ip stepen zaštite	IP40
Ik stepen zaštite	IK07
Temperatura okoline za rad uređaja	-25...60 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9,000 cm
Package 1 Width	29,500 cm
Package 1 Length	50,000 cm
Package 1 Weight	1,931 kg
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30,000 cm
Package 2 Width	40,000 cm
Package 2 Length	60,000 cm
Package 2 Weight	8,608 kg
Unit Type of Package 3	P12
Number of Units in Package 3	64
Package 3 Height	121,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	149,728 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Učinak u vezi sa sadržajem halogena	Proizvod bez halogena

Ugovorna garancija

Garancija	18 months
-----------	-----------