



Osnovne informacije

Grupa proizvoda	Spacial SDB
Primena uređaja	Više namena
Tip proizvoda ili komponente	Spojna kutija
Tip ormana	Prazan orman
Tip prednjeg poklopca	Niski puni poklopac
Boja	Svetlosiva (RAL 7035)

Dopunske informacije

Nazivna visina ormana	105 mm
Nazivna širina ormana	105 mm
Nazivna dubina ormana	49 mm
Montaža ormana	Montaža na zid
Sastav uređaja	1 telo 1 poklopac 1 zavrtnj poklopca
Fiksiranje poklopca	Zavrtnj
Materijal	Čelik
Završna obrada	Epoksi poliestar prah
Masa proizvoda	0,273 kg

Okruženje

Standardi	IEC 62208
IP stepen zaštite	IP55 u skladu sa IEC 60529
Ik stepen zaštite	IK07 conforming to IEC 62262

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,000 cm
Package 1 Width	10,500 cm
Package 1 Length	10,500 cm
Package 1 Weight	257,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	12,000 cm
Package 2 Width	24,000 cm
Package 2 Length	28,000 cm
Package 2 Weight	2,853 kg
Unit Type of Package 3	PAM
Number of Units in Package 3	1110
Package 3 Height	160,000 cm

Package 3 Width	100,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	343,890 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja