



Osnovne informacije

Grupa proizvoda	Linergy
Ime proizvoda	Linergy TR
Tip proizvoda ili komponente	Sabirnica
Kratko ime uređaja	TRA
Pribor / posebna kategorija	Pribor za povezivanje
Kompatibilnost proizvoda	TRV vijčani priključak priključni blok TRP pritiskom priključni blok TRR opružni priključni blok priključni blok TRH IDC priključni blok
Broj priključaka	10 priključaka

Dopunske informacije

Poprečni presek kablova	2,5 mm ²
Number of connections	2 3 4
Broj mernih ulaza	3 1 2 4 6
Količina po setu	Set od 10
Masa proizvoda	9 g
Boja	Crvena

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,0 cm
Package 1 Width	15,0 cm
Package 1 Length	17,0 cm
Package 1 Weight	8,0 g
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Height	15,0 cm
Package 2 Width	5,0 cm
Package 2 Length	17,0 cm
Package 2 Weight	88,0 g
Unit Type of Package 3	S02
Number of Units in Package 3	800
Package 3 Height	15,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	7,352 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Učinak u vezi sa sadržajem halogena	Proizvod sa plastičnim delovima bez halogena

Ugovorna garancija

Garancija	18 meseci
-----------	-----------