



Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Adapter
Broj polova	2P + E
Standard utičnice	Nemački

Dopunske informacije

[in] nazivna struja	16 A
Broj utičnica	1
Materijal utikača, utičnice	Kućište: samogasivi polimer
Materijal kontakta	Pinovi: poniklovan mesing
Masa proizvoda	0,16 kg
Boja poklopca	Plava

Okruženje

Standardi	EN 50250 IEC 60309-1 IEC 60309-2
Ip stepen zaštite	IP20 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-11

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,6 cm
Package 1 Width	5,8 cm
Package 1 Length	11,5 cm
Package 1 Weight	160,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,2 cm
Package 2 Width	26,8 cm
Package 2 Length	27,0 cm
Package 2 Weight	1,738 kg
Unit Type of Package 3	S03
Number of Units in Package 3	40
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm

Package 3 Length	40,0 cm
Package 3 Weight	7,439 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	У складу са изузецима
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------