

Tehničke karakteristike proizvoda

Karakteristike

NSYTRACR42

NSYTR krajnji poklopac za opružnu i utičnu
jednost. rednu stezaljku 1x1 - 4mm²



Osnovne informacije

Grupa proizvoda	Lineryg
Ime proizvoda	Lineryg TR
Tip proizvoda ili komponente	Poklopac
Kratko ime uređaja	TRA
Pribor / posebna kategorija	Izolacioni pribor
Kompatibilnost proizvoda	TRR opružni priključni blok priključni blok, length = 56 mm TRP pritiskom priključni blok, length = 56 mm
Debljina	2,2 mm

Dopunske informacije

Poprečni presek kabla	4 mm ²
Number of connections	2
Broj mernih ulaza	2
Količina po setu	Set od 50
Masa proizvoda	2,1 g
Boja	Siva

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,0 cm
Package 1 Width	20,0 cm
Package 1 Length	20,0 cm
Package 1 Weight	2,0 g
Unit Type of Package 2	BAG
Number of Units in Package 2	50
Package 2 Height	20,0 cm
Package 2 Width	2,0 cm
Package 2 Length	20,0 cm
Package 2 Weight	108,0 g
Unit Type of Package 3	S02
Number of Units in Package 3	800
Package 3 Height	15,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	2,068 kg

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovdanavedenih informacija.

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Učinak u vezi sa sadržajem halogena	Proizvod sa plastičnim delovima bez halogena

Ugovorna garancija

Garancija	18 months
-----------	-----------